

# Incounter crockery dispenser heated □70-120

P/N: 0162543 | EBR-TAS/H 70-120

**HUPFER**  
we make work flow



*Similar to illustration, technical modifications reserved. Without decoration.*

## Technical data

<b>Payload:</b>	40
<b>Capacity:</b>	600 W
<b>Supply voltage:</b>	220 V
<b>Nominal current:</b>	2,6 A
<b>Frequency:</b>	50 Hz
<b>Weight:</b>	20 kg
<b>Width:</b>	400 mm
<b>Depth:</b>	400 mm
<b>Height:</b>	821 mm

Cup dispenser for installation into a worktop, for storing three to eight stacks of round  $\varnothing$  2.8-4.7" (70-120 mm) cups, glasses and mugs in a statically heated stacking compartment. Designation formerly EBRH 70 - 120.

Dispenser in robust and hygienic design, made of high-quality stainless steel. Design for installation from above with shelf frame. Stacking compartment with stainless steel stacking platform and inner compartment panelling made of anodised-aluminium perforated plate to prevent crockery discolourations. Consistent output height thanks to manually adjustable stainless steel tension spring system. Easy cleaning of stacking compartment from above and via a cleaning opening in the base plate. Reduced temperature losses and heating time thanks to cover hood made of polycarbonate with 3-point locking mechanism. Heating through stainless steel tubular heating element, infinitely variable using thermostat toggle switch on the equipment, with temperature limiter as per VDE. Current supply via a connecting cable set consisting of two connecting cables with earthed plug and equipment plug and an On/Off switch with integrated indicator light as disconnecter.

The Hupfer incounter plate dispenser EBR-TAS/H 70-120 is used to save space when storing and handing out cups, glasses and mugs without using baskets by means of three to eight self-guided stacks on one stacking platform. The use of non-rusting stainless steel springs that are easy to insert and remove results in optimal adjustment options for different loads. The on/off switch can be conveniently integrated into the worktop and requires a cut-out measuring 30 × 22 mm.

Time and date of the request: 03.11.2025, 11:32:07 *All information / dimensions are approximate, technical changes reserved. © Hupfer*