

# Sterile goods transport cart for 9 StU

P/N: 7504845 | STW/M 9StE 1249/751/1469 DR

**HUPFER**  
we make work flow



## Technical data

<b>Payload:</b>	150 kg
<b>Weight:</b>	99 kg
<b>Width:</b>	1249 mm
<b>Depth:</b>	751 mm
<b>Height:</b>	1469 mm

*Similar to illustration, technical modifications reserved. Without decoration.*

Sterile supply transport trolley as universal means of transport for sterile supplies, durables and consumables as well as laundry and waste bags.

Trolley made entirely of high-quality stainless steel, self-supporting standard design. Single-walled transport trolley closed on all sides. The transport trolley is loaded on the long side via two double-walled double-wing doors that can be opened at an angle of 270°. The automatically-latching doors are attached to robust stainless steel hinges mounted on vertical push bars. A 2-point door lock with a transport latch and integrated sealing option in the upper section of the door, in combination with extensions to block the door lower edges, keep the doors safely closed during transport. The left door is additionally fitted with a stop bead, so together with the trolley profiling and the extra hygienic and easy to clean lip seals, optimum dust protection for the items to be transported is guaranteed. Extensions also serve to keep the doors open during loading, so no additional elements to be operated by a hand or foot are required. Rear wall with triple rolled bead for stiffening and sound insulation. Interior with wire shelf that is tiltable at three sides; in horizontal position for placing e.g. sterile and chemist's supplies, in vertical position as front safeguard, e.g. for inserted laundry or waste bags. Four continuous vertical push bars (2 per side) for manoeuvring even with the doors open. Inherently stable chassis design, suitable for delivery transport and adaptable to automatic trolley transport systems. Bumper protective feature provided by robust, continuous bumper strip that is effective even with the doors open, with frontal recesses for connecting a towing device to the chassis. Trolley runs on 2 swivel casters with total lock, 2 fixed casters, fastened by means of screw-on plates and several screws.

Time and date of the request:  
19.07.2025, 04:09:31

*All information / dimensions are approximate, technical changes reserved. © Hupfer*