

## Hook trolley set for StU container

P/N: 7506478 | HAW 605/620/1620 StE



### Technical data

<b>Weight:</b>	11 kg
<b>Width:</b>	605 mm
<b>Depth:</b>	620 mm
<b>Height:</b>	1620 mm

*Similar to illustration, technical modifications reserved. Without decoration.*

The hook trolley for StU containers is used for transporting and providing medical supplies in accessories attached to it.

The stainless steel hook trolley set for sterile goods units is used for convenient transport and user-friendly organisation of medical supplies in accessories attached to it. The Hupfer hook trolley ensures easy handling and efficient transport processes in any medical working environment. The all-round welded frame made of stainless steel square tube with curved upper corners is particularly torsion-resistant and robust. The frame also serves as a push bar. Firmly welded pairs of hooks make it easy to attach the appropriate accessories. Thus equipped, the hook trolley allows quick access and a clear overview of the supplies to be provided. The high-quality design guarantees optimum hygiene for demanding environments. The base of the trolley made of square tube with rounded corners and four swivel castors with two locks ensures smooth movement and precise manoeuvring. The antistatic tyres prevent electrostatic charging and provide effective protection against potential sparks Set consisting of a hook trolley with single side loading and 4 holders for StU containers

- Open design for fast access and user-friendly organisation
- Firmly welded pairs of hooks allow the accessories to be easily attached in the configuration required
- High-quality design guarantees easy cleaning and optimum hygiene
- Swivel castors ensure smooth movement and precise manoeuvring

Time and date of the request: 05.04.2026, 07:53:26 *All information / dimensions are approximate, technical changes reserved. © Hupfer*

## Hook trolley set for StU container

P/N: 7506478 | HAW 605/620/1620 StE

**HUPFER**  
we make work flow

- Locks guarantee safe movement and immobilisation
- Antistatic tyres prevent electrostatic charging and protect highly sensitive equipment

Time and date of the request:  
05.04.2026, 07:53:26

*All information / dimensions are approximate, technical changes reserved. © Hupfer*